

We are sorry that an old type motor has been discontinued so is available no longer. To install new DC motor, the following process should be done.

1. The motor shaft diameter was changed from 4mm to 5mm so please enlarge inner diameter of the gear to which motor shaft insert.
2. A part of motor flange, please refer to the attached sketch is also larger than old one so the hole of fixture should be shaped bigger.
3. Table cover will hit the motor so please cut a part off.

All modification is done by the customer in Japan as well.

(SM36-106-4202-21)
New DC Motor

Z-Axis replacement
spindle motor on SDX-10/30
(25m0-X-903)

